

Needle & Knockout Cylinders for Continuous Extrusion

Needle Cylinders		PHD MODEL
	See BCN 305825 Literature	
	25mm BORE x 20mm STROKE	ML310773
	50mm BORE x 30mm (1.181") STROKE	ML310701
	1-1/16" BORE x .800" STROKE	ML306733
	1-1/8" BORE x 1" STROKE	ML304949
	1-1/8" BORE x 1" STROKE	ML302933
	32mm BORE x 25mm STROKE	ML307865
	50mm x 35mm STROKE	ML308320
	50mm BORE x 25mm STROKE	ML307551
	1-1/8" BORE x 1" STROKE	ML307055

Knockout Cylinders		PHD MODEL
	20mm BORE x 5" STROKE	ML311385
	25mm BORE x 5" STROKE	ML311384
	AVK 1 3/8 x 2 -D-F-J	ML309752
	AVL 1-1/8 x 6 -L	ML311490
	AVL 1-1/8 x 5 -L	ML311491
	.875" DIA BORE x 1.000" +.030/- .000 STROKE (Non-rotating)	ML302973
	.875" DIA BORE x 1.000" STROKE	ML302056
	.875" DIA BORE x 1.000" STROKE	ML309942

GRE01

250 3/13 9000

