



FILLING LINE SOLUTIONS

Volumetric Pump ML# 302807




BENEFITS

- 303 stainless steel body, piston, piston rod, adjustment screws, and fasteners
- Adjustment screw for volume adjustment
- Additional Buna-N quad seal for added sealing and protection
- Compact design
- Other volumes and configurations available — contact PHD

SPECIFICATIONS	Volumetric Pump
UNIT WEIGHT	1 lb [454 g]
BORE SIZE	1 in [25.4 mm]
MINIMUM AIR PRESSURE	10 psi [0.7 bar]
MAXIMUM AIR PRESSURE	150 psi [10.3 bar]
TOTAL STROKE	.66 in [16.8 mm]
MAX. OPERATING TEMPERATURE	200°F [93°C]
DISPLACEMENT (AIR)	.553 in ³ [9.06 mL]
DISPLACEMENT (PUMP)	.292 in ³ [4.785 mL]

DIMENSIONS



- NOTES:**
- 1) DIMENSIONS ARE FOR REFERENCE ONLY
 - 2) ALL METRIC DIMENSIONS ARE GIVEN IN MILLIMETERS 1 mm = .03937 in

© Copyright 2011, by PHD, Inc. All Rights Reserved. Printed in the U.S.A.

CP302807A



PHD is a member of the
MAC Distributor Network

PHD, Inc. • P.O. Box 9070 • Fort Wayne, IN 46899 • (260) 747-6151 • FAX (260) 747-6754
www.phdinc.com • phdinfo@phdinc.com